




Specification		BB-800	BB-900	BB-1000
Power Rating		Australia or Europe: 220 – 240V~, 50/60Hz, 600 – 700W America or Canada: 120Vac, 60Hz, 660W		
Water inlet type	Type	Direct Inlet flow type		
	Water inlet pressure	0.4 ~ 7.5 kgf/cm <sup>2</sup> ( 5.69 psi ~ 106.7psi )		
Power cord		(1.2m (4 feet): AMERICA) / (1.8m:Australia or Europe)		
Wash Device	Posterior Wash	Max. 1.2 l /min ( Max. 0.32 GPM )		
	Feminine Wash	Max. 1.2 l /min ( Max. 0.32 GPM )		
	Water Pressure Adjustable	5 Levels		
	Warm Water Temperature	Room Temp ~ 40°C ( Room Temp. 104°F )		
	Heater	600 W		
	Safety Devices	Thermal fuse, Thermal switch, Float switch		
Heated Seat	Temperature	Room Temp ~ 41°C ( Room Temp. ~ 105.8°F )		
	Heater	55 W		
	Safety Device	Thermal fuse		
Warm Air Dryer Device	Adjustable Dry Temperature (Room Temp~45°C)			
	Heater (250W)	●	●	●
	Safety Device (Thermal fuse, bimetal)			
Turbo & Enema Function		●	●	●
Deodorizer		-	●	●
Remote control		-	-	●
Inlet water temperature		3°C ~ 35°C ( 37.4°F ~ 95°F )		
Ambient Temperature		3°C ~ 40°C ( 37.4°F ~ 104°F )		
Dimension	Elongated (Control)	Round (Control)	Elongated (Remote)	Round (Remote)
	W : 495mm (19.4 inch)	W : 495mm (19.4 inch)	W : 475mm (18.7 inch)	W : 475mm (18.7 inch)
	L : 525mm (20.6 inch)	L : 493mm (19.4 inch)	L : 525mm (20.6 inch)	L : 493mm (19.4 inch)
	H : 185mm (7.28 inch)	H : 185mm (7.28 inch)	H : 185mm (7.28 inch)	H : 185mm (7.28 inch)
Weight (kg)		5.3kg	5.4kg	5.2kg



## Features:

Side/Remote Control  
 Heated Seat  
 Power Saving  
 Hydraulic Seat  
 Seat Sensor  
 Built in Filter  
 3 in 1 Nozzle  
 Feminine Wash  
 Posterior Wash  
 Turbo Wash  
 Pulsating Massage  
 Oscillation  
 Self Cleaning  
 Air Drying  
 Self Diagnosis  
 Quick Release

Convenient panel to control and operate the various functions  
 Room Temp ~ 40°C  
 Two economy options  
 Gentle closing of seat and lid  
 Signals that the seat is occupied to commence cleaning operation  
 Protection against lime-scale build up  
 Patented nozzle for 3 cleansing programs  
 Soft aerated water spray for feminine cleansing  
 Soft yet powerful aerated water spray for thorough cleansing  
 Whirly mass of soft water spray to stimulate bowel movement  
 Pulsating and soothing flow of soft water  
 Oscillating movement of washing nozzle for thorough cleansing  
 Automatic self cleaning of washing nozzle before and after use  
 Powerful warm air-drying operation  
 System warns user of any malfunctions  
 Quick release mechanism to detach seat from toilet



Scanflex Ltd  
 2 Thursby Road  
 Croft Business Park  
 Bromborough  
 Wirral CH62 3PW  
 United Kingdom

t: +44 (0) 151 343 1523  
 f: +44 (0) 151 343 1514